

CLOSED COIL SPRING

These Closed Coil Springs deliver ideal forces for space closure maintenance applications, including Class II intra-arch maxillary retraction. The eyelet design allows versatile placement alternatives, while two lengths and four force ranges accommodate any application.



CLOSED COIL SPRING 10 PACK

FORCE	LENGTH	ITEM NUMBER
75gm (extra light)	9mm	60.40.110.09075
	12mm	60.40.110.12075
150gm (light)	9mm	60.40.120.09150
	12mm	60.40.120.12150
200gm (medium)	9mm	60.40.130.09200
	12mm	60.40.130.12200
250gm (heavy)	9mm	60.40.140.09250
	12mm	60.40.140.12250

CLOSED COIL SPRING 21" SPOOL

FORCE	LENGTH	ITEM NUMBER
75gm (extra light)	21"	60.40.112.21075
150gm (light)	21"	60.40.122.21150
200gm (medium)	21"	60.40.132.21200
250gm (heavy)	21"	60.40.142.21250

COIL SPRING SELECTION CHART

Size	Force Grams (x)	Stretch In mm to Obtain the (x) Force																			
		14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30			
9 MM	75																				
	150																				
	200																				
	250																				
12 MM	75																				
	150																				
	200																				
	250																				

If distance is larger than coil spring, metal ligature is suggested

■ WITHIN WORKING RANGE ■ IDEAL FORCE LEVELS
Courtesy of: Dr. Tomas Castellanos